



High efficiency with a crisp, sparkling light

MasterColor CDM PAR30L

Philips MasterColor® Ceramic Metal Halide PAR30L Lamps offer high-efficiency, ceramic metal halide reflector lamps with a stable color over lifetime and a crisp, sparkling light.

Benefits

- Philips MC PAR30L lamps deliver improved lumen maintenance over standard metal halide PAR lamps.
- Philips MC PAR30L lamps reduce lighting cost of ownership - they are an energy efficient alternative to incandescent or halogen PAR lamps.

Features

- Superior color stability— within $\pm 200K$
- Lamp to lamp color consistency over life higher lumen maintenance
- Improved lumen maintenance over standard metal halide
- Feature ALTO lamp technology with reduced mercury
- Operate on existing ballasts
- Lamps feature integrated UV blocking medium for reduced fading of fabrics and paintings
- 35 and 70 watt flood and spot, 3000, and 4000K versions

Application

- Ideal for retail accent and display lighting and architectural lighting for interior and exterior applications.

MasterColor CDM PAR30L

Warnings and Safety


- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Versions



PAR30L Med. Base

Dimensional drawing



Product	D	C (max)
MasterColor CDM70 PAR30L/M/FL/4K (942)	3.82 in	4.750 in

