



Environmentally Responsible Lamps

High Output T12

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Benefits

- Sustainable Lighting Solution -Less mercury and fewer lamps in landfills, combined with energy efficiency, reduces the impact on the environment.
- 12 month warranty period.
- TCLP compliant*
- * Fluorescent lamps that are TCLP compliant reduce the amount of pollutants released into the environment.

Features

- ALTO Lamp Technology.
- High light output.
- Available in 35,40,50,55,60,75,80,85,and 100 watts,in daylight, cool white, spec35, and ultralume colors.

Application

- Ideal for use in high bay applications such as warehouses, distribution centers and factories.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

High Output T12


Versions



R17d, T12

FA8, T12

Dimensional drawing



Product

F48T12/CW/HO ALTO 15PK

TL F96T12/CW/HO-O ALTO 110W FLUOR. LAMP

F96T12/CW/HO-O ALTO 8/2PK

F72T12/D/HO ALTO 15PK

F72T12/CW/HO ALTO 15PK

F48T12/D/HO ALTO 15PK

F96T12/D/HO-O ALTO 15PK

Product

F96T12/DX ALTO 15PK

Approval and application

Energy Saving Product Not Applicable

General information

Life 3-Hr Start [Hrs] 12000 h

Mechanical and housing

Bulb Shape T12

Approval and application

High Output T12

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
369785	F48T12/CW/HO ALTO 15PK	3.5 mg
369843	F48T12/D/HO ALTO 15PK	3.5 mg
366518	F72T12/CW/HO ALTO 15PK	6.8 mg
366534	F72T12/D/HO ALTO 15PK	6.8 mg

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
381764	F96T12/CW/HO-O ALTO 15PK	6.8 mg
205443	F96T12/CW/HO-O ALTO 8/2PK	6.8 mg
381774	F96T12/D/HO-O ALTO 15PK	6.8 mg
372821	F96T12/DX ALTO 15PK	6.8 mg

Operating and electrical

Order Code	Full Product Name	Power (Nom)
369785	F48T12/CW/HO ALTO 15PK	60 W
369843	F48T12/D/HO ALTO 15PK	60 W
366518	F72T12/CW/HO ALTO 15PK	85 W
366534	F72T12/D/HO ALTO 15PK	85 W

Order Code	Full Product Name	Power (Nom)
381764	F96T12/CW/HO-O ALTO 15PK	110 W
205443	F96T12/CW/HO-O ALTO 8/2PK	110 W
381774	F96T12/D/HO-O ALTO 15PK	110 W
372821	F96T12/DX ALTO 15PK	75 W

General information

Order Code	Full Product Name	Cap-Base
369785	F48T12/CW/HO ALTO 15PK	R17D
369843	F48T12/D/HO ALTO 15PK	R17D
366518	F72T12/CW/HO ALTO 15PK	R17D
366534	F72T12/D/HO ALTO 15PK	R17D

Order Code	Full Product Name	Cap-Base
381764	F96T12/CW/HO-O ALTO 15PK	R17D
205443	F96T12/CW/HO-O ALTO 8/2PK	R17D
381774	F96T12/D/HO-O ALTO 15PK	R17D
372821	F96T12/DX ALTO 15PK	FA8

Light technical

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color Temperature (Nom)	Color Rendering		
					Index (Nom)	Design Mean Lumens	Luminous Flux (Nom)
369785	F48T12/CW/HO ALTO 15PK	33	Cool White (CW)	4100 K	62	3500 lm	4050 lm
369843	F48T12/D/HO ALTO 15PK	54	Daylight	6500 K	79	3000 lm	3400 lm
366518	F72T12/CW/HO ALTO 15PK	33	Cool White (CW)	4100 K	62	5500 lm	6350 lm
366534	F72T12/D/HO ALTO 15PK	54	Daylight	6500 K	79	4850 lm	5600 lm
381764	F96T12/CW/HO-O ALTO 15PK	33	Cool White (CW)	4100 K	62	7650 lm	8800 lm
205443	F96T12/CW/HO-O ALTO 8/2PK	33	Cool White (CW)	4100 K	62	7650 lm	8800 lm
381774	F96T12/D/HO-O ALTO 15PK	54	Daylight	6500 K	79	6800 lm	7800 lm
372821	F96T12/DX ALTO 15PK	57	Daylight Deluxe	6500 K	90	4200 lm	4775 lm

