



Reduce your maintenance costs

PLUS T8 High Output

Philips PLUS T8 High Output 8-foot fluorescent lamps reduce the impact on the environment by offering long life and low mercury.

Benefits

- Low mercury - only 4.4 mg per lamps.
- 24 month Warranty Period.
- TCLP Compliant*
- * Fluorescent lamps that are TCLP Compliant reduce the amount of pollutants released into the environment.

Features

- Extends the relamping cycle which reduces maintenance and disposal costs.
- PLUS T8 HO 8-foot has the longest rated average life in the industry.
- 30,000 hours rated average life[◇]
- More light over life with 95% lumen maintenance than a MH 400/U at 67% lumen maintenance.
- Available in 8 foot length 86 watts with 3000, 3500 & 4100 Color Temperatures.
- [◇] Average life under engineering data with lamps turned off and restarted once every 12 operating hours.

Application

- Ideal for industrial applications requiring longer life.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


PLUS T8 High Output

Versions



R17d, T8

Dimensional drawing



Product

F96T8/TL841/HO/PLUS ALTO 25/1

F96T8/TL850/PLUS/HO/ALTO 25/1

Approval and application

Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg
Picogram Per Lumen Hour	24 pg/lm.h

Operating and electrical

Power (Nom)	86 W
-------------	------

General information

Cap-Base	R17D
Life 3-Hr Start [Hrs]	24000 h

Light technical

Color Rendering Index (Nom)	85
-----------------------------	----

Mechanical and housing

Bulb Shape	T8
------------	----

Light technical (1/2)

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color Temperature (Nom)	Design Mean Lumens
236885	F96T8/TL841/HO/PLUS ALTO 25/1	TL841	TL841	4100 K	7625 lm
236893	F96T8/TL850/PLUS/HO/ALTO 25/1	TL850	TL850	5000 K	7525 lm

Light technical (2/2)

Order Code	Full Product Name	Luminous Flux (Nom)
236885	F96T8/TL841/HO/PLUS ALTO 25/1	8200 lm

Order Code	Full Product Name	Luminous Flux (Nom)
236893	F96T8/TL850/PLUS/HO/ALTO 25/1	8100 lm

PLUS T8 High Output

