



Extra low mercury

T8 Standard

Philips T8 lamps are energy-efficient lighting solutions.

Benefits

- Better for the environment - only 1.7mg of mercury per lamp with ALTO II Technology
- Reduce maintenance costs by extending the relamping cycle

Features

- 95% lumen maintenance and reduced lamp-end blackening
- Available in multiple wattages: 17W, 25W and 32W
- Available in multiple color temperatures: 3000K, 3500K, 4100K, and 5000K

Application

- Ideal for applications requiring maximum maintained light output.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

T8 Standard


Versions



G13, T8

G13, T8

Dimensional drawing



Product

F17T8/TL850 ALTO 30PK
 F25T8/TL850 ALTO 30PK
 F25T8/TL841/ALTO 30PK
 F17T8/TL835/ALTO 30PK
 F17T8/TL841/ALTO 30PK
 F25T8/TL835/ALTO 30PK

Approval and application

Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	1.7 mg

General information

Cap-Base	G13
Life 12-Hr Instant Start [Hrs]	30000 h
Life 12-Hr Programstart [Hrs]	36000 h
Life 3-Hr Instant Start [Hrs]	24000 h
Life 3-Hr Program Start [Hrs]	30000 h

Mechanical and housing

Bulb Shape	T8
------------	----

Approval and application

Order Code	Full Product Name	Picogram Per Lumen Hour
281881	F17T8/TL835/ALTO 30PK	54 pg/lm.h
281899	F17T8/TL841/ALTO 30PK	54 pg/lm.h
281907	F25T8/TL835/ALTO 30PK	35 pg/lm.h
281915	F25T8/TL841/ALTO 30PK	35 pg/lm.h
280925	F25T8/TL850 ALTO 30PK	36 pg/lm.h
280909	F17T8/TL850 ALTO 30PK	54 pg/lm.h

Operating and electrical

Order Code	Full Product Name	Power (Nom)
281881	F17T8/TL835/ALTO 30PK	17 W
281899	F17T8/TL841/ALTO 30PK	17 W
281907	F25T8/TL835/ALTO 30PK	25 W

Order Code	Full Product Name	Power (Nom)
281915	F25T8/TL841/ALTO 30PK	25 W
280925	F25T8/TL850 ALTO 30PK	25 W
280909	F17T8/TL850 ALTO 30PK	17 W

Light technical (1/2)

T8 Standard

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)
281881	F17T8/TL835/ ALTO 30PK	TL835	TL835	3500 K	85
281899	F17T8/TL841/ ALTO 30PK	TL841	TL841	4100 K	85
281907	F25T8/TL835/ ALTO 30PK	TL835	TL835	3500 K	85

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)
281915	F25T8/TL841/ ALTO 30PK	TL841	TL841	4100 K	85
280925	F25T8/TL850 ALTO 30PK	TL850	TL850	5000 K	82
280909	F17T8/TL850 ALTO 30PK	TL850	TL850	5000 K	82

Light technical (2/2)

Order Code	Full Product Name	Design Mean Lumens	Luminous Flux (Nom)
281881	F17T8/TL835/ALTO 30PK	1310 lm	1375 lm
281899	F17T8/TL841/ALTO 30PK	1310 lm	1375 lm
281907	F25T8/TL835/ALTO 30PK	2045 lm	2150 lm

Order Code	Full Product Name	Design Mean Lumens	Luminous Flux (Nom)
281915	F25T8/TL841/ALTO 30PK	2045 lm	2150 lm
280925	F25T8/TL850 ALTO 30PK	1995 lm	2100 lm
280909	F17T8/TL850 ALTO 30PK	1235 lm	1300 lm

