



Brighten your home with infinite possibilities

DuraMax Reflector Flood

Philips DuraMax® Long Life Reflector Flood Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Available in a variety of sizes and wattages. Use flood lights for general or ambient lighting; use spot lights to highlight artwork or architecture. Both are ideal for use in recessed cans or track lighting fixtures.

Benefits

- Philips DuraMax long life reflector bulbs last longer than standard incandescent, significantly reducing the hassle of replacing light bulbs that burn out too quickly.
- Philips DuraMax reflector floods provide a wide beam of light for general ambient lighting; DuraMax reflector spots provide a narrow beam of light for accenting.

Features

- Lasts at Least One and a Half Years!
- Medium base.
- Available in a variety of wattages.
- Available in flood version for general or ambient lighting; Available in spot version to highlight artwork or architecture.
- Available in R20: 30, 50 and 75 watt; Br30 Flood: 45, 65, and 85 watt; BR30 Spot: 65 and 85 watt; BR40 Flood: 65, 85 and 120 watt; BR40 Spot: 120 watt.
- * Based on an average of hours usage per day/7 days per week. Hours differ between products, and there are exceptions. See individual products for details.

Application

- The DuraMax flood reflectors are ideal for general or ambient lighting in recessed cans or track lighting fixtures. The DuraMax Spot reflector highlights artwork and architecture.

DuraMax Reflector Flood

Versions



E26, BR30, Frosted




E26, R20, Reflector



E26, R20, Frosted

Dimensional drawing



Product

65BR30/FL55/LL 120V 6/2PK

65BR30/FL55/LL TP 120V 4/3

65BR30/FL55/LL 120V 4/3

Product	D	C (max)
45R20/LL 120V 6/1 TP	2.5 in	3.94 in
30R20/LL 120V 12/1 TP		
30R20/LL 120V 4/3 TP		

Operating and Electrical

Voltage (Nom) 120 V

General Information

Cap-Base E26

Operating Position Universal

Light Technical

Beam Description Flood

Approval and Application

DuraMax Reflector Flood

Order Code	Full Product Name	Estimated Energy Cost Per Year
166926	65BR30/FL55/LL 120V 6/2PK	7.83 \$
223040	65BR30/FL55/LL TP 120V 4/3	7.83 \$
167718	65BR30/FL55/LL 120V 4/3	7.83 \$

Order Code	Full Product Name	Estimated Energy Cost Per Year
223131	30R20/LL 120V 4/3 TP	-
167536	30R20/LL 120V 12/1 TP	-
433490	45R20/LL 120V 6/1 TP	-

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
166926	65BR30/FL55/LL 120V 6/2PK	65 W
223040	65BR30/FL55/LL TP 120V 4/3	65 W
167718	65BR30/FL55/LL 120V 4/3	65 W

Order Code	Full Product Name	Power (Rated) (Nom)
223131	30R20/LL 120V 4/3 TP	30 W
167536	30R20/LL 120V 12/1 TP	30 W
433490	45R20/LL 120V 6/1 TP	45 W

General Information

Order Code	Full Product Name	Life With 3		Rated Lifetime (Hours)
		Hour Per Day Use	Main Application	
166926	65BR30/FL55/LL 120V 6/2PK	2.3 a	Flood and Ambient Lighting	2500 h
223040	65BR30/FL55/LL TP 120V 4/3	2.3 a	Flood and Ambient Lighting	2500 h
167718	65BR30/FL55/LL 120V 4/3	2.3 a	Flood and Ambient Lighting	2500 h

Order Code	Full Product Name	Life With 3		Rated Lifetime (Hours)
		Day Use	Main Application	
223131	30R20/LL 120V 4/3 TP	-	-	-
167536	30R20/LL 120V 12/1 TP	-	-	-
433490	45R20/LL 120V 6/1 TP	-	Household	2500 h

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated		
			Color Temperature (Max)	Luminous Flux (Max)	Luminous Flux (Nom)
166926	65BR30/FL55/LL 120V 6/2PK	55 °	2710 K	620 lm	610 lm
223040	65BR30/FL55/LL TP 120V 4/3	55 °	2710 K	620 lm	610 lm
167718	65BR30/FL55/LL 120V 4/3	55 °	2710 K	620 lm	610 lm

Order Code	Full Product Name	Beam Angle (Nom)	Correlated		
			Color Temperature (Max)	Luminous Flux (Max)	Luminous Flux (Nom)
223131	30R20/LL 120V 4/3 TP	-	-	-	-
167536	30R20/LL 120V 12/1 TP	-	-	-	-
433490	45R20/LL 120V 6/1 TP	-	-	-	385 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
166926	65BR30/FL55/LL 120V 6/2PK	Frosted	BR30
223040	65BR30/FL55/LL TP 120V 4/3	Frosted	BR30
167718	65BR30/FL55/LL 120V 4/3	Frosted	BR30

Order Code	Full Product Name	Bulb Finish	Bulb Shape
223131	30R20/LL 120V 4/3 TP	Reflector	R-20 (R20)
167536	30R20/LL 120V 12/1 TP	Reflector	R-20 (R20)
433490	45R20/LL 120V 6/1 TP	Frosted	R-20 (R20)

DuraMax Reflector Flood

