



Incandescent Infrared Reflector Flood

Reflector Infrared R40

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Philips Infrared lamps are suited for heating and drying in industrial and commercial applications. These incandescent, gas-filled infrared heat lamps come up to full temperature almost immediately, eliminating costly warm-up time. Highly efficient heat generators produce a minimum of light rays and a high amount of infrared radiation. The BR40 lamp provides a built-in reflector for radiant energy control.

Features

- Available in clear and red. Comfortable warmth.
- Available in: Clear 375 watt and Red 250 watt.

Application

- Ideal for bathroom recessed fixtures and commercial applications.


Versions



E26, R40, Red

Reflector Infrared R40

Dimensional drawing



Product	C (max)
250R40 IR/HR/TG 120V 4/1	6.875 in

