



# MSD Platinum – The power to light your creativity

## MSD Platinum

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

### Benefits

- High beam intensity
- Freedom to create smaller and lighter fixtures
- High perceived brightness
- A long and reliable performance

### Features

- Very short arc
- Compact system
- High correlated color temperature
- Philips Platinum technology

### Application

- Events
- Shows/Theater
- Touring/Stage

# MSD Platinum

## Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

## Versions



MSD Platinum 2 R

## Dimensional drawing



Product	D (max)	T (max)	O	C (max)
MSD Platinum 2 R 1CT/8	46.5 mm	13.5 mm	1.2 mm	57.1 mm
MSD Platinum 2 R UNP/24	46.5 mm	13.5 mm	1.2 mm	57.1 mm

