



Reflector Flood

65BR/FL60 120V 24/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.


Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Base Up Horizontal (BUH) [Base Up Horizontal (BUH)]
Main Application	Flood and Ambient Lighting
Gas Filling	GAS
Life with 3 Hour Per Day Use	1.8 a
Footnote Incandescent 1	Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)
Rated Lifetime (Hours)	2000 h
Light Technical	
Beam Angle (Nom)	60 °
Initial lumen (Nom)	620 lm
Beam Description	Flood [Flood]
Operating and Electrical	
Power (Rated) (Nom)	65 W

Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Frosted
Cap-Base Information	Aluminium [Aluminium Cap]
Filament Shape	CC6 [Straight]
Bulb Shape	BR40 [BR40 (BR40)]
Approval and Application	
Estimated Energy Cost Per Year	7.83 \$
Product Data	
Order product name	65BR/FL60 120V 24/1
EAN/UPC - Product	046677225360
Order code	389130
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	920670036324
Net Weight (Piece)	0.001 kg

Reflector Flood

Dimensional drawing



Product

65BR/FL60 120V 24/1

65W E26 120V BR40 FL FR

