



# Reflector Flood

## 65BR/FL60 130V CDA 24/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.

### Product data

General information	
Base	E26 [ Single Contact Medium Screw]
Operating Position	Universal [ Universal]
Main Application	Indoor Reflector
Gas Filling	GAS
Life with 3 Hour Per Day Use	1.8 a
Footnote Incandescent 1	Consider the compact fluorescent lamps for energy savings.
Footnote Incandescent 2	Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)
Rated Lifetime (Hours)	2000 h
Light technical	
Beam Angle (Nom)	60 °
Initial lumen (Nom)	565 lm
Beam Description	Flood [ Flood]
Luminous Flux Lamp @ 120V	425 lm


Operating and electrical	
Power (Rated) (Nom)	65 W
Lamp Wattage Rated@120V	55 W
Voltage (Nom)	130 V
Mechanical and housing	
Bulb Finish	Frosted
Cap-Base Information	Aluminium [ Aluminium Cap]
Filament Shape	CC6 [ Straight]
Bulb Shape	BR40 [ BR40 (BR40)]
Approval and application	
Estimated Energy Cost Per Year at 120V	6.67 \$
Estimated Energy Cost Per Year	7.83 \$

Product data	
Order product name	65BR/FL60 130V CDA 24/1
EAN/UPC - Product	046677225377
Order code	225375
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	920670336103
Copy Net Weight (Piece)	0.002 lb

# Reflector Flood

---

## Dimensional drawing



### Product

65BR/FL60 130V CDA 24/1

65BR/FL60 130V CDA 24/1

