



Reflector Flood

300BR/FL 120/130V 24/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.


Product data

General information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Main Application	Indoor Reflector
Gas Filling	GAS
Footnote Incandescent 1	Circle E-The encircled E means this bulb meets Federal minimum efficiency standards.
Rated Lifetime (Hours)	2000 h
Light technical	
Beam Angle (Nom)	55 °
Initial lumen (Nom)	2480 lm
Beam Description	Flood [Flood]
Operating and electrical	
Power (Rated) (Nom)	300 W
Voltage (Nom)	120 V
Mechanical and housing	
Bulb Finish	Frosted

Cap-Base Information	Aluminium [Aluminium Cap]
Filament Shape	C11 [V-shape above glass button (cylindriform)]
Bulb Shape	BR40 [BR40 (BR40)]
Approval and application	
Approbation Marks	Circle E logo
Product data	
Order product name	300BR/FL 120/130V 24/1
EAN/UPC - Product	046677143435
Order code	143438
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	920673035502
Copy Net Weight (Piece)	0.002 lb

Reflector Flood

Dimensional drawing



Product

300BR/FL 120/130V 24/1

300BR/FL 120/130V 24/1

