



Reflector BR38 Flood

75BR30/PK CDA 120V 8/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These reflector lamps come in multiple colors ideal for holiday, party or special effects lighting.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Main Application	Indoor Reflector
Gas Filling	GAS
Life with 3 Hour Per Day Use	1.8 a
Footnote Incandescent 1	Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)
Footnote Incandescent 2	Circle E-The encircled E means this bulb meets Federal minimum efficiency standards.
Rated Lifetime (Hours)	2000 h

Light Technical

Beam Angle (Nom)	55°
Initial lumen (Nom)	555 lm
Beam Description	Flood [Flood]

Operating and Electrical

Power (Rated) (Nom)	75 W
---------------------	------

Voltage (Nom)	120 V
---------------	-------

Mechanical and Housing

Bulb Finish	Pink
Cap-Base Information	Aluminium [Aluminium Cap]
Filament Shape	CC6 [Straight]
Bulb Shape	BR30 [BR30 (BR30)]

Approval and Application


Estimated Energy Cost Per Year	9.03 \$
Approbation Marks	Circle E logo

Product Data

Order product name	75BR30/PK CDA 120V 8/1
EAN/UPC - Product	046677227395
Order code	249029
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8
Material Nr. (12NC)	920681336304
Net Weight (Piece)	0.001 kg

Reflector BR38 Flood

Dimensional drawing



Product

75BR30/PK CDA 120V 8/1

75W E26 120V BR30 FL Pink

