



# Reflector Agro

## 75BR30/ARGO CDA 120V 6/1 TP

Philips Family of Reflector Agro provide the perfect light to promote plant growth.


### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
Operating Position	Universal [ Universal]
Main Application	Agro
Gas Filling	GAS
Life with 3 Hour Per Day Use	1.8 a
Footnote Incandescent 1	Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)
Footnote Incandescent 2	Circle E-The encircled E means this bulb meets Federal minimum efficiency standards.
Rated Lifetime (Hours)	2000 h
Light Technical	
Beam Angle (Nom)	55°
Initial lumen (Nom)	700 lm
Beam Description	Flood [ Flood]
Operating and Electrical	
Power (Rated) (Nom)	75 W

Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Agro Blue
Cap-Base Information	Aluminium [ Aluminium Cap]
Filament Shape	CC6 [ Straight]
Bulb Shape	BR30 [ BR30 (BR30)]
Approval and Application	
Estimated Energy Cost Per Year	9.03 \$
Approbation Marks	Circle E logo
Product Data	
Order product name	75BR30/ARGO CDA 120V 6/1 TP
EAN/UPC - Product	046677415280
Order code	415281
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	920682436307
Net Weight (Piece)	0.011 kg

# Reflector Agro

## Dimensional drawing



### Product

75BR30/ARGO CDA 120V 6/1 TP

75W E26 120V BR30 FL Agro-Blue

