



InfraRed Industrial Heat Incandescent

R125 IR 375W E27 230-250V CL 1CT/10

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

Product data

General information	
Base	E27 [E27]
Operating Position	Universal [Universal]
Main Application	Infrared Industrial
Nominal Lifetime (Nom)	5000 h
Rated Lifetime (Hours)	5000 h

Operating and electrical	
Power (Rated) (Nom)	375 W
Voltage (Nom)	230-250 V

Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Bulb Finish	Clear


Bulb Material	Hard Glass
Bulb Shape	R125 [R 125mm]

Luminaire design requirements	
Bulb Temperature (Max)	932 °F

Product data	
Order product name	R125 IR 375W E27 230-250V CL 1CT/10
EAN/UPC - Product	8711500126597
Order code	250472
Numerator - Quantity Per Pack	1
Local code description	LAMP INCAN SEC-230V375-IMP
Numerator - Packs per outer box	10
Material Nr. (12NC)	923223543807
Net Weight (Piece)	0.302 lb

InfraRed Industrial Heat Incandescent

Dimensional drawing



R125 IR 375W E27 230-250V CL 1CT/10

Product	D	C (max)
R125 IR 375W E27 230-250V CL 1CT/10	4-15/16 in	7-1/4 in

