



DuraMax Reflector Flood

30R20/LL 120V 4/3 TP

Philips DuraMax® Long Life Reflector Flood Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Available in a variety of sizes and wattages. Use flood lights for general or ambient lighting; use spot lights to highlight artwork or architecture. Both are ideal for use in recessed cans or track lighting fixtures.

Product data

General Information		Mechanical and Housing	
Base	E26 [Single Contact Medium Screw]	Bulb Finish	Reflector
Operating Position	Universal [Universal]	Cap-Base Information	Aluminium [Aluminium Cap]
Footnote Incandescent 1	Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)	Filament Shape	CC6 [Straight]
		Bulb Shape	R-20 (R20)
Light Technical		Product Data	
Beam Description	Flood [Flood]	Order product name	30R20/LL 120V 4/3 TP
		EAN/UPC - Product	50046677223132
		Order code	223131
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	4
		Material Nr. (12NC)	923304736314
		Net Weight (Piece)	28.060 g
Operating and Electrical			
Power (Rated) (Nom)	30 W		
Voltage (Nom)	120 V		

DuraMax Reflector Flood

Dimensional drawing

Product

30R20/LL 120V 4/3 TP

30W E26 120V R20

