

PHILIPS

Lighting



Reflector PAR38 Krypton

K250PAR38/FL 120-130V 12PK

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These PAR Krypton flood lamps are available with medium skirted bases.

Product data

General information	
Base	E26/50X39 [Skirted Medium Screw (PAR Lamps)]
Operating Position	Universal [Universal]
Gas Filling	KRYPTON
Nominal Lifetime (Nom)	4000 h
Switching Cycle	2 times per 24 h; minimum 15 minutes off
Rated Lifetime (Hours)	4000 h

Light technical	
Beam Angle (Nom)	30 °
Initial lumen (Nom)	3100 lm
Luminous Intensity (Max)	5000 cd
Beam Description	Flood [Flood]
Color Rendering Index (Nom)	100

Operating and electrical	
Power (Rated) (Nom)	250 W
Voltage (Nom)	120-130 V

Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Eccentricity (Max)	1/16 in
Skewness (Max)	1/8 in
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]

Product data	
Order product name	Reflector 250W Med Skt 120-130V PAR38 FL 1CT
EAN/UPC - Product	046677374327
Order code	374322
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	923834636104
Copy Net Weight (Piece)	0.677 lb
ILCOS Code	IPAR-250-120/130-E26-121/30

Reflector PAR38 Krypton

Dimensional drawing

Product	D (max)	C (max)	C1
Reflector 250W Med Skt 120-130V PAR38 FL 1CT	4-7/8 in	5-5/16 in	4-13/16 in

Reflector 250W Med Skt 120-130V PAR38 FL 1CT

