



# Halogen reflector

## 13528 15W GZ4 6V 1CT/24

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

### Product data


General Information		Voltage (Nom)	
Base	GZ4 [ GZ4]	6 V	
Philips Code	13528	Controls and Dimming	
ANSI Code	-	Dimmable	Yes
LIF Code	-	Mechanical and Housing	
Operating Position	S105 [ s105]	Cap-Base Information	na [ -]
Main Application	Projection	Bulb Material	Quartz-UV Open
Life to 50% Failures (Nom)	750 h	Reflector Finish	Smooth
J Code	-	Filament Shape	-
Light Technical		Filament Dimensions WxH	-
Correlated Color Temperature (Nom)	2900 K	Bulb Shape	R35
Color Rendering Index (Nom)	100	Luminaire Design Requirements	
Operating and Electrical		Bulb Temperature (Max)	900 °C
Power (Rated) (Nom)	15 W	Pinch Temperature (Max)	350 °C

## Halogen reflector

Working Distance WD	92 mm
<b>Product Data</b>	
Order product name	13528 15W GZ4 6V 1CT/24
EAN/UPC - Product	8718696689936
Order code	324038

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	923883810105
Net Weight (Piece)	12.000 g

### Dimensional drawing



13528 15W GZ4 6V

Product	D (max)	C (max)
13528 15W GZ4 6V 1CT/24	35 mm	42 mm

