



# Halogen non-reflector

## 5761 30W 6V 100PK


Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

### Product data

General Information		Mechanical and Housing	
Base	G4 [ G4]	Bulb Material	Quartz-UV Open
Philips Code	5761	Filament Dimensions WxH	1.6x1.6
ANSI Code	-		
LIF Code	-		
Operating Position	Universal [ Universal]		
Main Application	Projection		
Life to 50% Failures (Nom)	100 h		
Light Technical		Luminaire Design Requirements	
Initial lumen (Nom)	765 lm	Bulb Temperature (Max)	900 °C
Correlated Color Temperature (Nom)	3200 K	Pinch Temperature (Max)	400 °C
Color Rendering Index (Nom)	100		
Operating and Electrical		Product Data	
Power (Rated) (Nom)	30 W	Order product name	5761 30W G4 6V
Voltage (Nom)	6 V	EAN/UPC - Product	8711500410849
		Order code	257139
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	100
		Material Nr. (12NC)	923931110103
		Net Weight (Piece)	0.001 kg

## Halogen non-reflector

### Dimensional drawing



5761 30W G4 6V

Product	D (max)	L (max)	C (max)
5761 30W G4 6V	9.5 mm	19.75 mm	31 mm

