



# Halogen reflector

## EKE 150W 21V 24PK

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

### Product data

General Information	
Cap-Base	GX5.3 [GX5.3]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	150 W
Voltage (Nom)	21 V
Voltage (Nom)	21 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Smooth
Product Data	
Full product code	871150041073330
Order product name	13629 150W GX5.3 21V 1CT/24
Order code	315929
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material number (12NC)	924010319894
Full product name	EKE 150W 21V 24PK
EAN/UPC - Case	8711500421616

## Halogen reflector

### Dimensional drawing



Product	D (max)	C (max)
13629 150W GX5.3 21V 1CT/24	50.7 mm	44.5 mm

