



MR16

35MR16/FL36 50PK

Philips Halogen MR16 lamps provide a bright white light for accent lighting. They make it easy to optimize the look and feel of your brand, your merchandise, and the shoppers experience, with lower operating costs.

Product data

General information	
Base	GU5.3 [GU5.3]
Philips Code	14598
Operating Position	Universal [Universal]
ANSI Code Halogen	FMW
Nominal Lifetime (Nom)	3000 h
Rated Lifetime (Hours)	3000 h

Light technical	
Beam Angle (Nom)	36 °
Luminous Intensity (Max)	1000 cd
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	100

Operating and electrical	
Power (Rated) (Nom)	35.0 W
Lamp Current (Nom)	3 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V

Controls and dimming	
Dimmable	Yes


Mechanical and housing	
Bulb Shape	MR16 [2inch/50mm]

Luminaire design requirements	
Bulb Temperature (Max)	482 °F
Cap-Base Temperature (Max)	662 °F

Product data	
Order product name	35MR16/FL36 50PK
EAN/UPC - Product	046677140564
Order code	140566
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material Nr. (12NC)	924047817126
Copy Net Weight (Piece)	0.066 lb
ILCOS Code	HRGI-35-12-GU5.3-50/36

MR16

Dimensional drawing



35MR16/FL36 50PK

Product	D (max)	C (max)
35MR16/FL36 50PK	2-1/16 in	1-13/16 in

