



Appliance Oven Tubular

APP 15W E14 230-240V T22 CL OV 1CT

Tubular vacuum lamps with clear glass (T-bulb)

Product data

General Information	
Base	E14 [E14]
Operating Position	Universal [Universal]
Main Application	Oven
Nominal Lifetime (Nom)	1000 h
Switching Cycle	4000X
Rated Lifetime (Hours)	1000 h
Flux measurement reference	Sphere

Light Technical	
Initial lumen (Nom)	85 lm
Luminous Flux (Rated) (Nom)	90 lm
Chromaticity Coordinate X (Nom)	0.46
Chromaticity Coordinate Y (Nom)	0.411
Correlated Color Temperature (Nom)	2700 K
Color Rendering Index (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	15.4 W
Lamp Current (Nom)	0.06 A
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light
Power Factor (Nom)	1

Voltage (Nom)	230-240 V
---------------	-----------

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T6 [T6]


Approval and Application	
Energy Efficiency Class	G
Energy Consumption kWh/1000 h	16 kWh
EPREL Registration Number	423229

Product Data	
Order product name	Appliance 15W E14 230-240V T22 CL OV 1CT
EAN/UPC - Product	8711500036599
Order code	250803
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	924196244440
Net Weight (Piece)	10.500 g
ILCOS Code	IBT/C-15-230/240-E14-22*

Appliance Oven Tubular

Dimensional drawing

Product	D (max)	C (max)
Appliance 15W E14 230-240V T22 CL OV 1CT	22 mm	49 mm



APP 15W E14 230-240V T22 CL OV

