



# Halogen reflector

## JCR 15V 150W H5 24 PACK

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

### Product data


General Information		Voltage (Nom)	
Base	GZ6.35 [ GZ6.35]	15 V	
Philips Code	NA [ -]	Controls and Dimming	
ANSI Code	-	Dimmable	Yes
LIF Code	-	Mechanical and Housing	
Operating Position	Base Down +/- 90 D [ Base Down +/- 90 D]	Cap-Base Information	na [ -]
Main Application	Fiber optic illumination	Bulb Material	Quartz-UV Open
Life to 50% Failures (Nom)	500 h	Reflector Finish	Smooth
J Code	JCR15V150W5H	Filament Shape	-
Light Technical		Filament Dimensions WxH	-
Correlated Color Temperature (Nom)	3100 K	Bulb Shape	R-16 [ R-16]
Color Rendering Index (Nom)	100	Luminaire Design Requirements	
Operating and Electrical		Bulb Temperature (Max)	900 °C
Power (Rated) (Nom)	150 W	Pinch Temperature (Max)	350 °C

## Halogen reflector

Working Distance WD	36 mm
<b>Product Data</b>	
Order product name	JCR 15V 150W H5 24 PACK
EAN/UPC - Product	8711500413291
Order code	249235

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	924793618594
Net Weight (Piece)	0.025 kg

### Dimensional drawing



JCR 15V 150W 5H

Product	D (max)	C (max)
JCR 15V 150W H5 24 PACK	50 mm	43 mm

