



Halogen Low Voltage

ELC-5 24V 250W 24PK

The long lifetime of most of the Halogen Low Voltage lamps is further extended by the unique P3 technology developed by Philips. This allows the lamp to be used at higher temperatures, thereby extending the lamp's lifetime, reducing early failures, and resulting in fewer maintenance man hour costs. P3 also ensures consistency of high-quality light output, and allows the lamp to be used in any burning position, which enables more compact fixture designs. In addition, the compact filament produces a clean white light and high beam intensity for true natural colors on stage and without any hotspots.


Product data

General Information	
Base	GX5.3 [GX5.3]
Philips Code	13163
ANSI Code	ELC-5H
LIF Code	-
Operating Position	Base Down +/- 90 D [Base Down +/- 90 D]
Main Application	Projection
Life to 50% Failures (Nom)	500 h
Light Technical	
Color Rendering Index (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	250 W
Voltage (Nom)	24 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Smooth
Filament Dimensions WxH	-
Bulb Shape	R-16 [R-16]
Luminaire Design Requirements	
Bulb Temperature (Max)	900 °C
Pinch Temperature (Max)	400 °C
Working Distance WD	32 mm
Product Data	
Order product name	13163 ELC/5H 250W GX5.3 24V ICT/24
EAN/UPC - Product	8711500413475
Order code	381665
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	924862720540
Net Weight (Piece)	0.024 kg

Halogen Low Voltage

Dimensional drawing



ELC/5H 250W GX5.3 24V

Product	D (max)	C (max)
13163 ELC/5H 250W GX5.3 24V 1CT/24	50 mm	44.5 mm

