



Double Ended Linear

Double Ended Linear BC500T3Q/CL/TP 120V 6/2PK

High-quality white light with superior lumen performance. Halogen Double Ended lamps provide bright, white light for work lights and security lighting. Rugged construction for busy work sites. Offered in several lengths to meet most application needs. High lumen output provides light where you need it.

Product data

General information	
Base	R7S [R7s]
Operating Position	Horizontal +/- 4 D [Horizontal +/- 4 D]
Nominal Lifetime (Nom)	2000 h
Rated Lifetime (Hours)	2000 h
Light technical	
Initial lumen (Nom)	9500 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	19 lm/W
Color Rendering Index (Nom)	100
Operating and electrical	
Power (Rated) (Nom)	500 W
Lamp Current (Nom)	4.17 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	120 V
Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Bulb Finish	Clear
Bulb Shape	T3 [T 12mm (T3)]

Luminaire design requirements	
Bulb Temperature (Max)	1652 °F
Pinch Temperature (Max)	662 °F
Pinch Temperature (Max)-DUP(do not use)	662 °F

Product data	
Order product name	Double Ended Linear BC500T3Q/CL/TP 120V 6/2PK
EAN/UPC - Product	50046677415728
Order code	415729
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	924883936301
Net Weight (Piece)	0.022 lb

Double Ended Linear

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Double Ended Linear BC500T3Q/CL/TP 120V 6/2PK	1/2 in	4-9/16 in	4-1/2 in	4-7/16 in	4-5/8 in

Double Ended Linear BC500T3Q/CL/TP 120V 6/2PK

