



Double Ended Linear

Double Ended Linear BC150T3Q/CL LONG 12/1

High-quality white light with superior lumen performance. Halogen Double Ended lamps provide bright, white light for work lights and security lighting. Rugged construction for busy work sites. Offered in several lengths to meet most application needs. High lumen output provides light where you need it.

Product data

General Information	
Lighting Technology	Halogen
Rated Lifetime (Hours)	2,000 hour(s)
Operating Position	P4 [Parallel +/-4D or Horizontal(HOR)]
Nominal lifetime	2,000 hour(s)
Cap-Base	R7S [R7s]

Light Technical	
Luminous Flux	2,000 lumen
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	13.3 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	150 W
Lamp Current (Nom)	1.25 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3 [T 12mm (T3)]

Product Data	
Order product name	BC150T3Q/CL LONG 12/1
Order code	415752
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material number (12NC)	924884836301
Full product name	Double Ended Linear BC150T3Q/CL LONG 12/1
EAN/UPC - Case	50046677415759

Double Ended Linear

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
BC150T3Q/CL LONG 12/1	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm

