



Double Ended Linear

Double Ended Linear BC300T3Q/CL/TP 120V 6/2PK

High-quality white light with superior lumen performance; Halogen Double Ended lamps provide bright, white light for work lights and security lighting. Rugged construction for busy work sites. Offered in several lengths to meet most application needs. High lumen output provides light where you need it.

Product data

General information		Mechanical and housing	
Base	R7S [R7s]	Bulb Finish	Clear
Operating Position	Horizontal +/- 4 D [Horizontal +/- 4 D]	Bulb Shape	T3 [T 12mm (T3)]
Nominal Lifetime (Nom)	2000 h	Luminaire design requirements	
Rated Lifetime (Hours)	2000 h	Bulb Temperature (Max)	900 °C
Light technical		Pinch Temperature (Max)	350 °C
Initial lumen (Nom)	5000 lm	Product data	
Correlated Color Temperature (Nom)	2900 K	Order product name	Double Ended Linear BC300T3Q/CL/TP 120V 6/2PK
Luminous Efficacy (rated) (Nom)	16 lm/W	EAN/UPC - Product	50046677415711
Color Rendering Index (Nom)	100	Order code	415711
Operating and electrical		Numerator - Quantity Per Pack	1
Power (Rated) (Nom)	300 W	Numerator - Packs per outer box	6
Lamp Current (Nom)	2.5 A	Material Nr. (12NC)	924884936301
Starting Time (Nom)	0.0 s	Copy Net Weight (Piece)	0.022 lb
Voltage (Nom)	120 V		
Controls and dimming			
Dimmable	Yes		

Double Ended Linear

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Double Ended Linear BC300T3Q/CL/TP 120V 6/2PK	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm

Double Ended Linear BC300T3Q/CL/TP 120V 6/2PK

