



# Reflector Flood

## 45R20 130V 12/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.

### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
Operating Position	Universal [ Universal]
Main Application	Indoor Reflector
Gas Filling	GAS
Rated Lifetime (Hours)	2000 h
Light Technical	
Initial lumen (Nom)	380 lm
Beam Description	Flood [ Flood]
Operating and Electrical	
Power (Rated) (Nom)	45 W
Voltage (Nom)	130 V
Mechanical and Housing	
Bulb Finish	Frosted

Cap-Base Information	Aluminium [ Aluminium Cap]
Filament Shape	CC6 [ Straight]
Bulb Shape	R-20 (R20)
Product Data	
Order product name	45R20 130V 12/1
EAN/UPC - Product	046677203221
Order code	203224
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	925154436103
Net Weight (Piece)	0.028 kg

## Reflector Flood

### Dimensional drawing

Product	C (max)
45R20 130V 12/1	3.94 in

45W E26 130V R20

