



# DuraMax Reflector Flood

## 45R20/LL 120V 6/1 TP

Philips DuraMax® Long Life Reflector Flood Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Available in a variety of sizes and wattages. Use flood lights for general or ambient lighting; use spot lights to highlight artwork or architecture. Both are ideal for use in recessed cans or track lighting fixtures.

### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
Operating Position	Universal [ Universal]
Main Application	Household
Gas Filling	GAS
Rated Lifetime (Hours)	2500 h

  

Light Technical	
Initial lumen (Nom)	385 lm
Beam Description	Flood [ Flood]

  

Operating and Electrical	
Power (Rated) (Nom)	45 W
Voltage (Nom)	120 V

  

Mechanical and Housing	
Bulb Finish	Frosted

Cap-Base Information	Aluminium [ Aluminium Cap]
Filament Shape	CC6 [ Straight]
Bulb Shape	R-20 (R20)

  

Product Data	
Order product name	45R20/LL 120V 6/1 TP
EAN/UPC - Product	046677203238
Order code	433490
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	925154636310
Net Weight (Piece)	28.060 g

## DuraMax Reflector Flood

### Dimensional drawing

Product	D	C (max)
45R20/LL 120V 6/1 TP	2.5 in	3.94 in

45W E26 120V R20

