



Reflector Infrared BR40, PAR38

250BR40 IR/1/TG 120V 4/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Philips Infrared lamps are suited for heating and drying in industrial and commercial applications. These incandescent, gas-filled infrared heat lamps come up to full temperature almost immediately, eliminating costly warm-up time. Highly efficient heat generators that produce a minimum of light rays and a high amount of infrared radiation. The BR40 lamp provides a built-in reflector for radiant energy control.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Main Application	Infrared
Gas Filling	GAS
Footnote Incandescent 1	Average laboratory life in excess of 5000 hours. In-service life depends upon service conditions. (27)
Footnote Incandescent 2	Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)
Footnote Incandescent 3	Circle E-The encircled E means this bulb meets Federal minimum efficiency standards.
Rated Lifetime (Hours)	5000 h

Light Technical	
Beam Description	Spot
Operating and Electrical	
Power (Rated) (Nom)	250 W
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear
Cap-Base Information	Aluminium [Aluminium Cap]
Filament Shape	C-9 [Pendant]
Bulb Shape	BR40 [BR40 (BR40)]
Product Data	
Order product name	250BR40 IR/1/TG 120V 4/1
EAN/UPC - Product	046677202057
Order code	202051
Numerator - Quantity Per Pack	1


Reflector Infrared BR40,PAR38

Numerator - Packs per outer box 4

Material Nr. (12NC) 925255136307

Net Weight (Piece) 0.001 kg

Dimensional drawing



250W E26 120V BR40 SP CL

Product

250BR40 IR/1/TG 120V 4/1

