



Reflector Infrared R40

250R40 IR/HR/TG 120V 4/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Philips Infrared lamps are suited for heating and drying in industrial and commercial applications. These incandescent, gas-filled infrared heat lamps come up to full temperature almost immediately, eliminating costly warm-up time. Highly efficient heat generators produce a minimum of light rays and a high amount of infrared radiation. The BR40 lamp provides a built-in reflector for radiant energy control.

Product data

General information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Main Application	Household
Gas Filling	GAS
Footnote Incandescent 1	Circle E-The encircled E means this bulb meets Federal minimum efficiency standards.
Rated Lifetime (Hours)	5000 h

Light technical	
Beam Description	Flood [Flood]

Operating and electrical	
Power (Rated) (Nom)	250 W
Voltage (Nom)	120 V

Mechanical and housing	
Bulb Finish	Red


Cap-Base Information	Brass [Brass Cap]
Bulb Material	Hard Glass
Filament Shape	C-9 [Pendant]
Bulb Shape	R40 [R40 (R40)]

Approval and application	
Approbation Marks	Circle E logo

Product data	
Order product name	250R40 IR/HR/TG 120V 4/1
EAN/UPC - Product	046677159320
Order code	159327
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	925272736308
Net Weight (Piece)	0.002 lb

Reflector Infrared R40

Dimensional drawing



Product	C (max)
250R40 IR/HR/TG 120V 4/1	6.875 in

250R40 IR/HR/TG 120V 4/1

