



Halogen PAR

Halogen 72PAR38/EVP/FL25 120V 12/1

Halogen PAR lamps reduce energy consumption without sacrificing the qualities of a traditional PAR lamp. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar PAR20, PAR30S, PAR30L, and PAR38 shapes. Use them in existing fixtures just as you would standard halogen PAR lamps.


Product data

General Information	
Base	E26/50X39 [Skirted Medium Screw (PAR Lamps)]
Operating Position	Universal [Universal]
Main Application	Outdoor (OD)
Gas Filling	GAS
Rated Lifetime (Hours)	1100 h
Light Technical	
Beam Angle (Nom)	25 °
Initial lumen (Nom)	1350 lm
Luminous Intensity (Nom)	2000 cd
Beam Description	Flood [Flood]
Correlated Color Temperature (Nom)	2900 K
Color Rendering Index (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	72 W
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Clear
Cap-Base Information	Brass [Brass Cap]
Bulb Material	Hard Glass
Reflector Finish	Aluminized
Filament Shape	CC-8 [Axial]
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Product Data	
Order product name	Halogen 72PAR38/EVP/FL25 120V 12/1
EAN/UPC - Product	046677428938
Order code	428938
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	925706536306
Net Weight (Piece)	0.350 kg

Halogen PAR

Dimensional drawing



Product

Halogen 72PAR38/EVP/FL25 120V 12/1

PAR38 STD 72W E26/50x39/BRC 120V FL 25D

