



Halogen PAR

Halogen 39PAR20/EVP/SP10 120V 15/1

Halogen PAR lamps reduce energy consumption without sacrificing the qualities of a traditional PAR lamp. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar PAR20, PAR30S, PAR30L, and PAR38 shapes. Use them in existing fixtures just as you would standard halogen PAR lamps.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Main Application	Track, Downlighting & Outdoor
Gas Filling	GAS
Rated Lifetime (Hours)	1100 h
Light Technical	
Beam Angle (Nom)	10 °
Initial lumen (Nom)	500 lm
Luminous Intensity (Nom)	4150 cd
Beam Description	Spot
Correlated Color Temperature (Nom)	2900 K
Color Rendering Index (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	39 W
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear

Cap-Base Information	Brass [Brass Cap]
Bulb Material	Hard Glass
Reflector Finish	Aluminized
Filament Shape	CC-8 [Axial]
Bulb Shape	PAR20 [PAR 2.5 inch]

Approval and Application

Estimated Energy Cost Per Year	6.02 \$
--------------------------------	---------

Product Data


Order product name	Halogen 39PAR20/EVP/SP10 120V 15/1
EAN/UPC - Product	046677425128
Order code	425124
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	925707436302
Net Weight (Piece)	0.092 kg

Halogen PAR

Dimensional drawing

Product

Halogen 39PAR20/EVP/SP10 120V 15/1



PAR20 39W E26/Brass 120V SP 10D

