



Halogen PAR

Halogen 39PAR30S/EVP/FL25 120V 15/1

Halogen PAR lamps reduce energy consumption without sacrificing the qualities of a traditional PAR lamp. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar PAR20, PAR30S, PAR30L, and PAR38 shapes. Use them in existing fixtures just as you would standard halogen PAR lamps.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Main Application	Track, Downlighting & Outdoor
Gas Filling	GAS
Life with 3 Hour Per Day Use	2.7 a
Rated Lifetime (Hours)	1100 h
Light Technical	
Beam Angle (Nom)	25 °
Initial lumen (Nom)	530 lm
Luminous Intensity (Nom)	2250 cd
Beam Description	Flood [Flood]
Color Rendering Index (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	39 W
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear

Cap-Base Information	Brass [Brass Cap]
Bulb Material	Hard Glass
Reflector Finish	Aluminized
Filament Shape	CC-8 [Axial]
Bulb Shape	PAR30S [PAR 3.75 inch/95mm Short]

Approval and Application	
Estimated Energy Cost Per Year	6.02 \$


Product Data	
Order product name	Halogen 39PAR30S/EVP/FL25 120V 15/1
EAN/UPC - Product	046677428969
Order code	428960
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	925709736302
Net Weight (Piece)	0.200 kg

Halogen PAR

Dimensional drawing

Product

Halogen 39PAR30S/EVP/FL25 120V 15/1



HAL PAR30S 39W E26/Brass 120V FL 25D

