



# Halogen PAR

## Halogen 53PAR30S/EVP/WFL40 120V 15/1

Halogen PAR lamps reduce energy consumption without sacrificing the qualities of a traditional PAR lamp. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar PAR20, PAR30S, PAR30L, and PAR38 shapes. Use them in existing fixtures just as you would standard halogen PAR lamps.

### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
Operating Position	Universal [ Universal]
Main Application	Indoor Reflector
Gas Filling	GAS
Rated Lifetime (Hours)	1100 h

Light Technical	
Beam Angle (Nom)	40 °
Initial lumen (Nom)	920 lm
Beam Description	Wide Flood [ Wide Flood]
Luminous Flux Lamp @ 120V	920 lm
Correlated Color Temperature (Nom)	2900 K
Color Rendering Index (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	53 W
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Clear
Cap-Base Information	NP-Nickelplated
Bulb Material	Hard Glass
Reflector Finish	Aluminized
Filament Shape	CC-8 [ Axial]
Bulb Shape	PAR30S [ PAR 3.75 inch/95mm Short]


Product Data	
Order product name	Halogen 53PAR30S/EVP/WFL40 120V 15/1
EAN/UPC - Product	046677428983
Order code	428986
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	925714136301
Net Weight (Piece)	0.190 kg

# Halogen PAR

## Dimensional drawing

### Product

Halogen 53PAR30S/EVP/WFL40 120V 15/1



HAL PAR30S 53W E26 120V WFL 40D

