

# T8 Plus

## F32T8/TL841 PLUS ALTO HV 30PK

Philips PLUS T8 lamps are energy-efficient lighting solutions and offer long life.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General information	
Base	G13 [ Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	44000 h
Life 12-Hr Instant Start [Hrs]	36000 h
Life 3-Hr Program Start [Hrs]	38000 h
Life 3-Hr Instant Start [Hrs]	30000 h
Features	ALTO® Plus
Footnotes Fluorescent/CFL 1	Circle E- The encircled E means this bulb meets Federal minimum efficiency standards.

### Light technical

Color Code	TL841 [ CCT of 4100K (841)]
Initial lumen (Nom)	2950 lm
Color Designation	TL841
Design Mean Lumens	2800 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	85

### Operating and electrical

Power (Rated) (Nom)	32 W
---------------------	------

### Mechanical and housing

Cap-Base Information	Green Base
----------------------	------------


Nominal Length (Inch)	48
Bulb Shape	T8 [ T8 (T8)]

### Approval and application

Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	20 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg

### Product data

Order product name	F32T8/TL841 PLUS ALTO HV 30PK
EAN/UPC - Product	046677281793
Order code	281790
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927852084104
Copy Net Weight (Piece)	0.3 lb




## T8 Plus

### Dimensional drawing

**Product**

F32T8/TL841 PLUS ALTO HV 30PK



F32T8/TL841 PLUS ALTO HV 30PK

