



PLUS T8 Slimline

F96T8/TL841 PLUS ALTO 25/1

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Warnings and Safety

· Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Base	FA8 [FA8]
Life 3-Hr Start [Hrs]	24000 h
Life 12-Hr Start [Hrs]	30000 h
Features	ALTO® Plus
Footnotes Fluorescent/CFL 1	This Bulb Meets US Federal Minimum Efficiency Standard.

Light Technical	
Color Code	TL841 [CCT of 4100K (841)]
Initial lumen (Nom)	5900 lm
Color Designation	TL841
Design Mean Lumens	5490 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	85


Operating and Electrical	
Power (Rated) (Nom)	59 W

Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	96
Bulb Shape	T8 [T8 (T8)]

Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	33 pg/lm.h
Mercury (Hg) Content (Nom)	4.4 mg

Product Data	
Order product name	F96T8/TL841 PLUS ALTO 25/1
EAN/UPC - Product	046677236854
Order code	236851
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927874584106
Net Weight (Piece)	0.001 kg




PLUS T8 Slimline

Dimensional drawing

Product

F96T8/TL841 PLUS ALTO 25/1



F96T8 59W/841 ALTO Plus ES

