



PLUS T8 Slimline

F96T8/TL850 PLUS ALTO 25/1

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Warnings and Safety

· Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Base	FA8 [FA8]
Life 3-Hr Start [Hrs]	24000 h
Life 12-Hr Start [Hrs]	30000 h
Features	ALTO® Plus
Footnotes Fluorescent/CFL 1	This Bulb Meets US Federal Minimum Efficiency Standard.

Light Technical

Color Code	TL850 [CCT of 5000K (850)]
Initial lumen (Nom)	5780 lm
Color Designation	TL850
Design Mean Lumens	5375 lm
Correlated Color Temperature (Nom)	5000 K
Color Rendering Index (Nom)	85

Operating and Electrical

Power (Rated) (Nom)	59 W
---------------------	------

Mechanical and Housing

Cap-Base Information	Green Base
----------------------	------------


Nominal Length (Inch)	96
Bulb Shape	T8 [T8 (T8)]

Approval and Application

Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	34 pg/lm.h
Mercury (Hg) Content (Nom)	4.4 mg

Product Data

Order product name	F96T8/TL850 PLUS ALTO 25/1
EAN/UPC - Product	046677236861
Order code	236869
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927874585008
Net Weight (Piece)	0.335 kg




PLUS T8 Slimline

Dimensional drawing

Product

F96T8/TL850 PLUS ALTO 25/1



F96T8 59W/850 ALTO Plus ES

