



High Output T12

F48T12/D/HO ALTO 15PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General information	
Base	R17D [R17d (RDC)]
Life 3-Hr Start [Hrs]	12000 h
Features	ALTO® (ALTO)
Footnotes Fluorescent/CFL 1	Approximate initial lumens are for 800 ma. operation. For 1000 ma. operation, lumens are approximately 10% higher and watts approximately 15% higher. (207)
Footnotes Fluorescent/CFL 2	Econ-o-watt® lamps are only recommended for use on high power factor lead, indoor ballasts that meet ANSI standards. The lamps are not recommended for use in drafty areas, or locations where the ambient temperature is less than 60°F, except as noted. Also they should not be operated on low power factor ballasts, reduced light or reduced current ballasts, dimming ballasts or emergency system inverter ballasts. (214)
Light technical	
Color Code	54
Initial lumen (Nom)	3400 lm

Color Designation	Daylight
Design Mean Lumens	3000 lm
Correlated Color Temperature (Nom)	6500 K
Color Rendering Index (Nom)	79
Operating and electrical	
Power (Rated) (Nom)	60 W
Mechanical and housing	
Cap-Base Information	Green Base
Nominal Length (Inch)	48
Bulb Shape	T12 [T12 (T12)]
Approval and application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	3.5 mg
Product data	
Order product name	F48T12/D/HO ALTO 15PK

High Output T12

EAN/UPC - Product	046677369842
Order code	369843
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15

Material Nr. (12NC)	927890205402
Copy Net Weight (Piece)	0.518 lb

Dimensional drawing

Product	F48T12/D/HO ALTO 15PK
---------	-----------------------

F48T12/D/HO ALTO 15PK

