



PL-L Long 4-Pin Base

PL-L 24W/830/4P 1CT/25

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

· Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Lamp Current (Nom)		0.345 A
Base	2G11 [2G11]	Voltage (Nom)	87 V	
Life to 50% Failures (Nom)	15000 h	Controls and Dimming		
Life to 50% Failures Preheat (Nom)	20000 h	Dimmable	Yes	
Light Technical		Mechanical and Housing		
Color Code	830 [CCT of 3000K]	Bulb Finish	Silicon	
Initial lumen (Nom)	1800 lm	Cap-Base Information	4P	
Color Designation	Warm White (WW)	Product Data		
Lumen Maintenance 10000 h (Nom)	92 %	Order product name	PL-L 24W/830/4P 1CT/25	
Lumen Maintenance 2000 h (Nom)	94 %	EAN/UPC - Product	046677345051	
Lumen Maintenance 5000 h (Nom)	93 %	Order code	345058	
Correlated Color Temperature (Nom)	3000 K	Numerator - Quantity Per Pack	1	
Luminous Efficacy (rated) (Nom)	75 lm/W	Numerator - Packs per outer box	25	
Color Rendering Index (Nom)	>80	Material Nr. (12NC)	927903308321	
Operating and Electrical		Net Weight (Piece)	82.000 g	
Power (Rated) (Nom)	24.0 W			

PL-L Long 4-Pin Base

ILCOS Code

FSD-24/30/1B-E-2G11


Dimensional drawing




Product	D (max)	D1 (max)	C (max)
PL-L 24W/830/4P	39.0 mm	18.0 mm	321.6 mm

PL-L 24W/830/4P Silicon

Photometric data



LDPB_PLLSIL_830-Spectral power distribution B/W



LDPO_PLLSIL_830-Spectral power distribution Colour

