



# PL-L Long 4-Pin Base

## PL-L 36W/841/4P 1CT/25

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General information	
Base	2G11 [ 2G11]
Life to 50% Failures (Nom)	15000 h
Life to 50% Failures Preheat (Nom)	20000 h

Light technical	
Color Code	841 [ CCT of 4100K (841)]
Initial lumen (Nom)	2900 lm
Color Designation	Cool White (CW)
Lumen Maintenance 10000 h (Nom)	92 %
Lumen Maintenance 2000 h (Nom)	94 %
Lumen Maintenance 5000 h (Nom)	93 %
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color Rendering Index (Nom)	82

Operating and electrical	
Power (Rated) (Nom)	36.0 W
Lamp Current (Nom)	0.435 A
Voltage (Nom)	106 V

Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Bulb Finish	Silicon
Cap-Base Information	4P


Product data	
Order product name	PL-L 36W/841/4P 1CT/25
EAN/UPC - Product	046677345136
Order code	345132

## PL-L Long 4-Pin Base

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927904508421
Copy Net Weight (Piece)	0.229 lb

ILCOS Code	FSD-36/40/1B-E-2G11
------------	---------------------



### Dimensional drawing



Product	D (max)	D1 (max)	C (max)
PL-L 36W/841/4P	1-9/16 in	3/4 in	16-7/16 in

PL-L 36W/841/4P

### Photometric data



LDPB\_PLLSIL\_840-Spectral power distribution B/W

LDPO\_PLLSIL\_840-Spectral power distribution Colour

