



PL-T Triple 4-Pin Base Energy Advantage

PL-T 32W/835/XEW/A/4P/27W 1CT/5X10 ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General information	
Base	GX24Q-3 [GX24q-3]
Life to 50% Failures Preheat (Nom)	16000 h
Features	ALTO® (ALTO)

Light technical	
Color Code	835 [CCT of 3500K]
Initial lumen (Nom)	1900 lm
Color Designation	White (WH)
Lumen Maintenance 2000 h (Nom)	92 %
Lumen Maintenance 5000 h (Nom)	87 %


Operating and electrical	
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	70 lm/W
Color Rendering Index (Nom)	82
Power (Rated) (Nom)	28 W
Lamp Current (Nom)	0.320 A

Controls and dimming	
Dimmable	Yes

PL-T Triple 4-Pin Base Energy Advantage

Mechanical and housing	
Cap-Base Information	4P
Approval and application	
Mercury (Hg) Content (Nom)	1.4 mg
Product data	
Order product name	PL-T 32W/835/XEW/A/4P/27W 1CT/5X10 ALTO
EAN/UPC - Product	046677220228

Order code	220228
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927906983520
Copy Net Weight (Piece)	0.154 lb





Dimensional drawing

Product	D (max)	B (max)	C (max)
PL-T 32W/835/XEW/A/4P/ALTO 27W	41.0 mm	123.0 mm	138.7 mm

PL-T 32W/835/XEW/A/4P/ALTO 27W

Photometric data



LDPB_PLT4PXEW_835-Spectral power distribution B/W

LDPO_PLT4PXEW_835-Spectral power distribution Colour

