



# PL-L Long 4-Pin Base

## PL-L 40W/830/4P/RS/IS 1CT/25

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Warnings and Safety


- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information		Voltage (Nom)	
Cap-Base	2G11 [2G11]		126 V
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	Yes
Luminous Flux	3,500 lumen	Product Data	
Color Designation	Warm White (WW)	Order product name	PL-L 40W/830/4P/RS/IS 1CT/25
Correlated Color Temperature (Nom)	3000 K	Order code	300426
Luminous Efficacy (rated) (Nom)	87 lm/W	Numerator - Quantity Per Pack	1
Color rendering index (CRI)	82	Numerator - Packs per outer box	25
Operating and Electrical		Material number (12NC)	927908008329
Power Consumption	36.3 W	Full product name	PL-L 40W/830/4P/RS/IS 1CT/25
Lamp Current (Nom)	0.320 A	EAN/UPC - Case	50046677111781
Voltage (Nom)	126 V		


# PL-L Long 4-Pin Base

## Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-L 40W/830/4P/RS/IS 1CT/25	39.0 mm	18.0 mm	539.2 mm	565 mm	571.6 mm

## Photometric data



Spectral Power Distribution Colour - PL-L 40W/830/4P/RS/IS 1CT/25

