



# PL-T Triple 4-Pin Base Energy Advantage

## PL-T 42W/835/XEW/A/4P/33W 1CT/5X10 ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050


### Product data

General information		Correlated Color Temperature (Nom)	
Base	GX24Q-4 [ GX24q-4]	3500 K	
Life to 50% Failures Preheat (Nom)	16000 h	Luminous Efficacy (rated) (Nom)	67 lm/W
Features	ALTO® (ALTO)	Color Rendering Index (Nom)	82
Light technical		Operating and electrical	
Color Code	835 [ CCT of 3500K]	Power (Rated) (Nom)	34.5 W
Initial lumen (Nom)	2300 lm	Lamp Current (Nom)	0.320 A
Color Designation	White (WH)	Controls and dimming	
Lumen Maintenance 2000 h (Nom)	92 %	Dimmable	Yes
Lumen Maintenance 5000 h (Nom)	87 %		


# PL-T Triple 4-Pin Base Energy Advantage

<b>Mechanical and housing</b>	
Cap-Base Information	4P
<b>Approval and application</b>	
Mercury (Hg) Content (Nom)	1.4 mg
<b>Product data</b>	
Order product name	PL-T 42W/835/XEW/A/4P/33W 1CT/5X10 ALTO
EAN/UPC - Product	046677220280

Order code	220285
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927908183520
Copy Net Weight (Piece)	0.183 lb





## Dimensional drawing



Product	D (max)	B (max)	C (max)
PL-T 42W/835/XEW/A/4P/ALTO 33W	41.0 mm	145.0 mm	160.7 mm

PL-T 42W/835/XEW/A/4P/ALTO 33W

## Photometric data



LDPB\_PLT4PXEW\_835-Spectral power distribution B/W

LDPO\_PLT4PXEW\_835-Spectral power distribution Colour

