



PL-T Triple 4-Pin Base

PL-T 26W/827/A/4P 1CT/5X10BOX ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information		Operating and Electrical	
Base	GX24Q-3 [GX24q-3]	LLMF 4000 h Rated	88 %
LSF Preheat 2000 h Rated	99 %	LLMF 6000 h Rated	85 %
LSF Preheat 4000 h Rated	98 %	LLMF 8000 h Rated	84 %
LSF Preheat 6000 h Rated	97 %	LLMF 12000 h Rated	81 %
LSF Preheat 8000 h Rated	90 %		
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	Power (Rated) (Nom)	27.0 W
Initial lumen (Nom)	1750 lm	Lamp Current (Nom)	0.335 A
Luminous Flux (Rated) (Nom)	1750 lm		
Color Designation	Incandescent White	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	Yes
Luminous Efficacy (rated) (Nom)	64.8 lm/W		
Color Rendering Index (Nom)	82		
LLMF 2000 h Rated	92 %		


PL-T Triple 4-Pin Base

Mechanical and Housing	
Cap-Base Information	4P
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	PL-T 26W/827/A/4P 1CT/5X10BOX ALTO
EAN/UPC - Product	046677384401
Order code	458240

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927910982750
Net Weight (Piece)	64.000 g
ILCOS Code	FSM-26/27/1B-E-GX24q=3




Dimensional drawing




PL-T ALTO 26W/827/4P A

Product	D (max)	A (max)	B (max)	C (max)
PL-T 26W/827/A/4P/ALTO	41 mm	86.7 mm	111.0 mm	126.7 mm

Photometric data




LDPB_PLTTOP4P_827-Spectral power distribution B/W



LDPO_PLTTOP4P_827-Spectral power distribution Colour


PL-T Triple 4-Pin Base

Lifetime



LDLM_PLTTOP4P_0001-Lumen maintenance diagram

LDLE_PLTTOP4P_0001-Life expectancy diagram



LDLE_PLTTOP4P_0002-Life expectancy diagram

