



PL-T Triple 4-Pin Base

PL-T 57W/841/A/4P 1CT/5X10BOX ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		LLMF 2000 h Rated		92 %	
Base	GX24Q-5 [GX24q-5]	LLMF 4000 h Rated	88 %		
Life to 50% Failures Preheat (Nom)	13000 h	LLMF 6000 h Rated	85 %		
LSF Preheat 2000 h Rated	99 %	LLMF 8000 h Rated	84 %		
LSF Preheat 4000 h Rated	98 %	LLMF 12000 h Rated	81 %		
LSF Preheat 6000 h Rated	97 %				
LSF Preheat 8000 h Rated	90 %				
Light Technical		Operating and Electrical			
Color Code	841 [CCT of 4100K]	Power (Rated) (Nom)	51.0 W		
Initial lumen (Nom)	4300 lm	Lamp Current (Nom)	0.320 A		
Luminous Flux (Rated) (Nom)	3900 lm				
Color Designation	Cool White (CW)	Temperature			
Correlated Color Temperature (Nom)	4100 K	Design Temperature (Nom)	28 °C		
Luminous Efficacy (Rated) (Min)	76 lm/W				
Color Rendering Index (Nom)	82	Controls and Dimming			
		Dimmable	Yes		

PL-T Triple 4-Pin Base

Mechanical and Housing	
Cap-Base Information	4P
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	PL-T 57W/841/A/4P 1CT/5X10BOX ALTO
EAN/UPC - Product	046677146337

Order code	146332
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927914084020
Net Weight (Piece)	101.000 g
ILCOS Code	FSM-57/40/1B-E-GX24q=5


Dimensional drawing




PL-T ALTO 57W/841/4P A

Product	D (max)	A (max)	B (max)	C (max)
PL-T 57W/841/A/4P	41 mm	157.7 mm	182.0 mm	197.7 mm

Lifetime




LDLM_PLTTOP4P_0001-Lumen maintenance diagram



LDLE_PLTTOP4P_0001-Life expectancy diagram

PL-T Triple 4-Pin Base

Lifetime



LDLE_PLTTOP4P_0002-Life expectancy diagram

