



MASTER TL5 Circular

TL5C 55W/830 1CT/10

This circular TL5 lamp (tube diameter 16 mm) offers extended design possibilities. The slim tube allows the creation of extremely flat luminaires and enables omnidirectional light distribution. It is suitable for a wide range of professional and semi-professional applications, and is ideal for use in shops, offices and public areas with unconventional layouts.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General information	
Base	2GX13 [2GX13]
Life to 50% Failures Preheat (Nom)	12000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	96 %
LSF Preheat 8000 h Rated	89 %
LSF Preheat 16000 h Rated	10 %
LSF Preheat 20000 h Rated	1 %
Flux measurement reference	Sphere


Light technical	
Color Code	830 [CCT of 3000K]
Initial lumen (Nom)	4210 lm

Luminous Flux (Rated) (Nom)	4200 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.44
Chromaticity Coordinate Y (Nom)	0.403
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	76 lm/W
Color Rendering Index (Nom)	81
LLMF 2000 h Rated	91 %
LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	84 %
LLMF 8000 h Rated	81 %
LLMF 12000 h Rated	77 %
LLMF 16000 h Rated	74 %


MASTER TL5 Circular

LLMF 20000 h Rated	72 %
Operating and electrical	
Power (Rated) (Nom)	55.7 W
Lamp Current (Nom)	0.550 A
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Shape	C-T5 [C-T 16 mm]
Approval and application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	4 mg
Mercury (Hg) Content (Nom)	4 mg
Energy Consumption kWh/1000 h	56 kWh

EPREL Registration Number	423622
Product data	
Order product name	MASTER TL5 Circular 55W/830 1CT/10
EAN/UPC - Product	8711500642790
Order code	165936
Numerator - Quantity Per Pack	1
Local code description	8344336
Numerator - Packs per outer box	10
Material Nr. (12NC)	927965783013
Net Weight (Piece)	0.243 lb
ILCOS Code	FSCH-55/30/1B-L/P-2GX13-16




Dimensional drawing




MASTER TL5 Circular 55W/830 1CT/10

Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
MASTER TL5 Circular 55W/830 1CT/10	3/4 in	9/16 in	11-9/16 in	12-1/16 in	10-1/4 in	10-3/4 in

Photometric data





LDPB_TL5-C8_830-Spectral power distribution B/W



LDPO_TL5-C8_830-Spectral power distribution Colour


MASTER TL5 Circular

Lifetime



LDLE_TL5-C8_0001-Life expectancy diagram

LDLE_TL5-C8_0002-Life expectancy diagram



LDLM_TL5-C8_0001-Lumen maintenance diagram

