



T5 Preheat

F6T5/CW PH 25PK

Philips T5 Fluorescent Lamps are incredibly powerful, environmentally responsible, long life lamps with an ultra-slim profile. This translates into reduced maintenance and disposal costs and also allows the use of smaller fixtures—which reduces ceiling clutter.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General information	
Base	G5 [G5]
Life To 10% Failures (Nom)	5000 h
Life to 50% Failures (Nom)	10000 h
Life to 50% Failures Preheat (Nom)	10000 h
System Description	na [-]
Light technical	
Color Code	33-640
Initial lumen (Nom)	260 lm
Color Designation	Cool White (CW)
Lumen Maintenance 10000 h (Nom)	58 %
Lumen Maintenance 2000 h (Nom)	75 %
Lumen Maintenance 5000 h (Nom)	70 %
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	43 lm/W
Color Rendering Index (Nom)	60

Operating and electrical	
Power (Rated) (Nom)	6.0 W
Lamp Current (Nom)	0.160 A
Voltage (Nom)	42 V
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and application	
Mercury (Hg) Content (Nom)	4.4 mg
Energy Consumption kWh/1000 h	7 kWh
Product data	
Order product name	F6T5/CW FAM/25
EAN/UPC - Product	046677114633


T5 Preheat

Order code	332411
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928000503321
Copy Net Weight (Piece)	0.046 lb

ILCOS Code	FD-6/41/2B-E-G5
------------	-----------------




Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
F6T5/CW FAM/25	16 mm	212.1 mm	219.2 mm	216.8 mm	226.3 mm

F6T5/CW FAM/25

Photometric data



LDPB_TL-MINI_33-640-Spectral power distribution B/W



LDPO_TL-MINI_33-640-Spectral power distribution Colour

