



Actinic BL TL(-K)/TL-D(-K)

Actinic BL TL-DK 36W/10 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Operating and Electrical	
Base	G13 [Medium Bi-Pin Fluorescent]	Power (Rated) (Nom)	36 W
Main Application	Insect traps	Lamp Current (Nom)	0.865 A
Life to 50% Failures (Nom)	9000 h	Voltage (Nom)	50 V
Useful Life (Nom)	5000 h		
Light Technical		Mechanical and Housing	
Color Code	10	Bulb Shape	T8 [T8]
Color Designation	Actinic		
Chromaticity Coordinate X (Nom)	225	Approval and Application	
Chromaticity Coordinate Y (Nom)	230	Mercury (Hg) Content (Nom)	8.0 mg

Actinic BL TL(-K)/TL-D(-K)

UV	
UV-B/UV-A (IEC)	0.2 %
UV-A Radiation 100Hr (IEC)	8.8 W
Product Data	
Order product name	Actinic BL TL-DK 36W/10 1SL/25
EAN/UPC - Product	8727900860832

Order code	286724
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928019701003
Net Weight (Piece)	68.900 g


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-DK 36W/10 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

TL-DK 36W/10

Photometric data



XDPB_XUATLDK_10-Spectral power distribution B/W



XDPO_XUATLDK_10-Spectral power distribution Colour

