



MasterColor CDM-T6

CDM150/T6/830 12PK

MasterColor CDM lamp gives a unique combination of unbeatable light quality and consistent performance over lifetime while keeping running costs low. The Philips MasterColor Tubular Single-Ended T6 lamp is a compact, energy efficient, ceramic metal halide lamp that provides crisp, sparkling light.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General information			
Base	G12 [G12]	Luminous Flux (Rated) (Min)	11700 lm
Operating Position	Universal [Universal]	Luminous Flux (Rated) (Nom)	13000 lm
Life to 5% Failures (Nom)	9000 h	Color Designation	Warm White (WW)
Life To 10% Failures (Nom)	10000 h	Lumen Maintenance 10000 h (Nom)	60 %
Life to 20% Failures (Nom)	11000 h	Lumen Maintenance 2000 h (Min)	65 %
Life to 50% Failures (Nom)	12000 h	Lumen Maintenance 2000 h (Nom)	75 %
ANSI Code HID	C142/E	Lumen Maintenance 5000 h (Min)	60 %
		Lumen Maintenance 5000 h (Nom)	70 %
		Chromaticity Coordinate X (Nom)	0.436
		Chromaticity Coordinate Y (Nom)	0.396
		Correlated Color Temperature (Nom)	3000 K
Light technical			
Color Code	830 [CCT of 3000K]		

MasterColor CDM-T T6

Luminous Efficacy (rated) (Nom)	88 lm/W
Color Rendering Index (Nom)	88

Operating and electrical

Power (Rated) (Nom)	150.1 W
Lamp Current Run-Up (Max)	2.5 A
Lamp Current (EM) (Nom)	1.8 A
Ignition Supply Voltage (Max)	198 V
Ignition Peak Voltage (Max)	5000 V
Ignition Supply Voltage (Min)	198 V
Ignition Peak Voltage (Min)	3500 V
Re-Ignition Time (Min) (Max)	15 min
Ignition Time (Max)	30 s
Voltage (Max)	106 V
Voltage (Min)	86 V
Voltage (Nom)	96 V

Controls and dimming

Dimmable	No
Run-Up Time 90% (Max)	3 min

Mechanical and housing

Bulb Finish	Clear
Bulb Shape	T6 [Diameter: 6/8 inch/19 mm]

Approval and application

Mercury (Hg) Content (Nom)	14.3 mg
Energy Consumption kWh/1000 h	162 kWh

UV

Pet (Niosh) (Min)	8 h/500lx
Damage Factor D/fc (Max)	0.3


Luminaire design requirements

Bulb Temperature (Max)	1202 °F
Cap-Base Temperature (Max)	536 °F
Pinch Temperature (Max)	662 °F

Product data

Order product name	CDM150/T6/830 12PK
EAN/UPC - Product	046677232726
Order code	232728
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928083705115
Copy Net Weight (Piece)	0.073 lb
ILCOS Code	MT/UB-150/830-H-G12-21/100

Dimensional drawing





CDM150/T6/830 12PK

Product	D (max)	D	O	L (min)	L (max)	L	C (max)
CDM150/T6/830 12PK	20 mm	0.75 in	9 mm	55 mm	57 mm	56 mm	110 mm


MasterColor CDM-T T6

Photometric data



LDPO_CDM-T_150W_830-Spectral power distribution Colour

Lifetime



LDLM_CDM-T_150W_830-Lumen maintenance diagram

