



MasterColor CDM-T6

CDM150/T6/942 12PK

MasterColor CDM lamp gives a unique combination of unbeatable light quality and consistent performance over lifetime while keeping running costs low. The Philips MasterColor Tubular Single-Ended T6 lamp is a compact, energy efficient, ceramic metal halide lamp that provides crisp, sparkling light.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General information	
Base	G12 [G12]
Operating Position	Universal [Universal]
Life to 5% Failures (Nom)	9000 h
Life To 10% Failures (Nom)	10000 h
Life to 20% Failures (Nom)	11000 h
Life to 50% Failures (Nom)	12000 h
ANSI Code HID	C142/E
Light technical	
Color Code	942 [CCT of 4200K]

Luminous Flux (Rated) (Min)	10900 lm
Luminous Flux (Rated) (Nom)	12100 lm
Color Designation	Cool White (CW)
Lumen Maintenance 10000 h (Nom)	70 %
Lumen Maintenance 2000 h (Min)	75 %
Lumen Maintenance 2000 h (Nom)	85 %
Lumen Maintenance 5000 h (Min)	70 %
Lumen Maintenance 5000 h (Nom)	80 %
Chromaticity Coordinate X (Nom)	0.375
Chromaticity Coordinate Y (Nom)	0.363
Correlated Color Temperature (Nom)	4200 K

MasterColor CDM-T T6

Luminous Efficacy (rated) (Nom)	82 lm/W
Color Rendering Index (Nom)	96

Operating and electrical

Power (Rated) (Nom)	150.1 W
Lamp Current Run-Up (Max)	2.5 A
Lamp Current (EM) (Nom)	1.9 A
Ignition Supply Voltage (Max)	198 V
Ignition Peak Voltage (Max)	5000 V
Ignition Supply Voltage (Min)	198 V
Ignition Peak Voltage (Min)	3500 V
Re-Ignition Time (Min) (Max)	15 min
Ignition Time (Max)	30 s
Voltage (Max)	98 V
Voltage (Min)	82 V
Voltage (Nom)	90 V

Controls and dimming

Dimmable	No
Run-Up Time 90% (Max)	3 min

Mechanical and housing

Bulb Finish	Clear
Bulb Shape	T6 [Diameter: 6/8 inch/19 mm]

Approval and application

Mercury (Hg) Content (Nom)	10.4 mg
----------------------------	---------

Energy Consumption kWh/1000 h	162 kWh
-------------------------------	---------

UV


Pet (Niosh) (Min)	8 h/500lx
Damage Factor D/fc (Max)	0.4

Luminaire design requirements


Bulb Temperature (Max)	1202 °F
Cap-Base Temperature (Max)	536 °F
Pinch Temperature (Max)	662 °F

Product data

Order product name	CDM150/T6/942 12PK
EAN/UPC - Product	046677373696
Order code	373696
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928084605115
Copy Net Weight (Piece)	0.073 lb
ILCOS Code	MT/UB-150/942-H-G12-21/100



Dimensional drawing




CDM150/T6/942 12PK



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
CDM150/T6/942 12PK	20 mm	0.75 in	8 mm	55 mm	57 mm	56 mm	110 mm

MasterColor CDM-T T6

Photometric data



Lifetime



LDLE_CDM-T_150W_942-Life expectancy diagram

LDLM_CDM-T_150W_942-Lumen maintenance diagram

