



MSR Gold™ FastFit

MSR Gold™ 700/2 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		Operating and Electrical	
Cap-Base	PGJX50 [PGJX50]	Luminous Efficacy (rated) (Nom)	68 lm/W
Operating Position	UNIVERSAL [Any or Universal (U)]	Color rendering index (CRI)	73
Light Technical		Controls and Dimming	
Color Code	2	Dimmable	Yes
Luminous Flux	48,000 lumen		
Chromaticity Coordinate X (Nom)	298		
Chromaticity Coordinate Y (Nom)	322		
Correlated Color Temperature (Nom)	7500 K		

MSR Gold™ FastFit

Product Data

Full product code	872790090850300
Order product name	MSR Gold 700/2 FastFit 1CT/8
Order code	245621
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8

Material number (12NC)

928106205114


Full product name

MSR Gold™ 700/2 FastFit 1CT/8

EAN/UPC - Case


8727900908510

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold 700/2 FastFit 1CT/8	23.2 mm	3.8 mm	64 mm	66 mm	65 mm	112 mm	50 mm

Photometric data



Spectral Power Distribution Colour - MSR Gold 700/2 FastFit 1CT/8

